



Reliability Test Result Report

LSI Type : BH2221FV-E2
 Package Type : SSOP-B20

PASS

【 Reliability Test Result 】

ITEM	TEST METHOD		DURATION	n	Pn
*2 Resistance to soldering heat	After the moisture soaking treatment,carry out the soldering heat stress(IR reflow .peak260°C)	JEITA ED4701-301	10sec	22	0
*1 Pressure Cooker	Storage at 121°C/100% (2.026x10 ⁵ Pa)	-	96hour	22	0
*1 Temperature Cycling	Tstg min (30min) / Tstg max (30min)	JEITA ED4701-105	100cycles	22	0
High Temperature Storage	Storage at Tstg max	JEITA ED4701-201	1000hours	22	0
Low Temperature Storage	Storage at Tstg min	JEITA ED4701-202	1000hours	22	0
*1 Temperature Humidity Storage	Place at 85°C/85%	JEITA ED4701-103	1000hours	22	0
*1 Temperature Humidity Bias	Apply the specified voltage at 85°C/85%	JEITA ED4701-102	1000hours	22	0
High Temperature Operation Life	Apply the specified voltage at Topr max	JEITA ED4701-101	1000hours	22	0
				(pcs)	(pcs)

【 Strength Test Result 】

ITEM	TEST METHOD		DURATION	n	Pn
Terminal strength	Pull force = 1N	JEITA ED4701-401	10sec	5	0
Solderability	Dipping temperature 215°C, (Pb)	JEITA ED4701-303	10sec	22	0
	Dipping temperature 245°C, (Pb free)	JEITA ED4701-303	5sec	22	0
Electro Static Discharge	C=100pF, R=1.5kΩ, 3times, ±2000V				
	HBM (Human Body Model)	JEITA ED4701-304	-	5	0
	C=200pF, R=0Ω, 3times, ±200V				
	MM (Machine Model)	-	-	5	0
	±750V				
	CDM (Charged Device Model)	JESD22-C101	-	5	0
Latch Up	Pulse current injection, trigger pulse current ±100mA	JEITA ED4701-306	-	5	0
				(pcs)	(pcs)

<*1> Soldering Heat examination is executed 3 times for the precondition.

<*2> Moisture soaking treatment Standard : 85°C 85% 168h / Dry packing : 30°C 70% 192h

Yoshitaka Ichise

General Manager
 Quality Control Division
 LSI Production Headquarters
 ROHM Co., Ltd.

Notes

- 1) The information contained herein is subject to change without notice.
- 2) Before you use our Products, please contact our sales representative and verify the latest specifications :
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Products beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrant that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting from non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>